



Top plate, F3A-flanges, for WxD=1350x800mm, IP55, grey

Part no. XSPTF13508
133007
EL Number 2465942
(Norway)

General specifications		
Product name		Eaton xEnergy Main LV switchgear
Part no.		XSPTF13508
EAN		4015081299188
Product Length/Depth		1260 millimetre
Product height		30 millimetre
Product width		700 millimetre
Product weight		11.5 kilogram
Compliances		RoHS conform
Product Tradename		xEnergy Main
Product Type		LV switchgear
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton xEnergy Main LV switchgear
Globally Marketable		Yes

Technical data ETIM 9.0

Cabinet enclosures (EG000011) / Top-/floor element (enclosure/cabinet) (EC000744)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Roof element (electrical cabinet) / Top cover/top cover element (electrical cabinet) (ecl@ss13-27-18-24-05 [ACN616016])		
Suitable for roof planking		Yes
Suitable for bottom planking		Yes
Width	mm	700
Height	mm	30
Depth	mm	1260
Suitable for enclosure building width	mm	1350
Suitable for enclosure building depth	mm	800
Material		Steel
Surface finishing		Powder coating
Colour		Grey
RAL-number		7035
With de-aeration		No
Suitable for outdoor set-up		No
With cable entry		Yes