



Section wide door, glass window, HxW=1625x592mm, IP55, grey

**Part no. XTSZDSKW-H1625W592
177273**

General specifications		
Product name		Eaton xEnergy Main LV switchgear
Part no.		XTSZDSKW-H1625W592
EAN		4015081717262
Product Length/Depth		35 millimetre
Product height		1615 millimetre
Product width		592 millimetre
Product weight		21.5 kilogram
Compliances		RoHS conform
Product Tradename		xEnergy Main
Product Type		LV switchgear
Product Sub Type		None

Technical data ETIM 9.0

Cabinet enclosures (EG000011) / Door/operating panel (enclosure/cabinet) (EC000747)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Door (electrical cabinet) / Door/operating panel (enclosure) (ecl@ss13-27-18-22-04 [ACN614016])		
Model		Stop door
Version as glazed door		Yes
Version as door for disconnecting switch interlocking		No
Width	mm	592
Height	mm	1615
Depth	mm	35
EMC-version		No
Material		Steel
Surface finishing		Powder coating
Colour		Grey
Degree of protection (IP)		IP55
Degree of protection (NEMA)		4X