

Leerwert
Standard-
sprache
(Datei inaktiv)

Top panel, Alu, D=800mm

Part no.

**XSPTU08A
178053**

| General specifications | | |
|----------------------------|--|--|
| Product name | | Eaton xEnergy Main LV switchgear |
| Part no. | | XSPTU08A |
| EAN | | 4015081733286 |
| Product Length/Depth | | 662 millimetre |
| Product height | | 76.5 millimetre |
| Product width | | 172 millimetre |
| Product weight | | 1.94 kilogram |
| Compliances | | RoHS conform |
| Product Tradename | | xEnergy Main |
| Product Type | | LV switchgear |
| Product Sub Type | | None |
| Public Consumption | | Yes |
| PDH Status | | Active |
| Product Family Description | | ES-PMCC-PDC-Eaton xEnergy Main LV switchgear |
| Globally Marketable | | Yes |

Technical data ETIM 9.0

| | | |
|--|----|-----------|
| Cabinet enclosures (EG000011) / Top-/floor element (enclosure/cabinet) (EC000744) | | |
| Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Roof element (electrical cabinet) / Top cover/top cover element (electrical cabinet) (ecl@ss13-27-18-24-05 [ACN616016]) | | |
| Suitable for roof planking | | Yes |
| Suitable for bottom planking | | Yes |
| Width | mm | 172 |
| Height | mm | 76.5 |
| Depth | mm | 662 |
| Suitable for enclosure building width | mm | 800 |
| Suitable for enclosure building depth | mm | 800 |
| Material | | Aluminium |
| Surface finishing | | Primed |
| Colour | | Grey |
| RAL-number | | 0 |
| With de-aeration | | No |
| Suitable for outdoor set-up | | No |
| With cable entry | | Yes |