



Top panel, WxD=425x800mm, IP42, grey

Part no. **XSPTV40408**  
**178058**

General specifications		
Product name		Eaton xEnergy Main LV switchgear
Part no.		XSPTV40408
EAN		4015081733330
Product Length/Depth		682 millimetre
Product height		89 millimetre
Product width		332 millimetre
Product weight		3.9 kilogram
Compliances		RoHS conform
Product Tradename		xEnergy Main
Product Type		LV switchgear
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton xEnergy Main LV switchgear
Globally Marketable		Yes

### Technical data ETIM 9.0

Cabinet enclosures (EG000011) / Top-/floor element (enclosure/cabinet) (EC000744)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Roof element (electrical cabinet) / Top cover/top cover element (electrical cabinet) (ecl@ss13-27-18-24-05 [ACN616016])		
Suitable for roof planking		Yes
Suitable for bottom planking		Yes
Width	mm	332
Height	mm	89
Depth	mm	682
Suitable for enclosure building width	mm	425
Suitable for enclosure building depth	mm	800
Material		Steel
Surface finishing		Powder coating
Colour		Grey
RAL-number		7035
With de-aeration		Yes
Suitable for outdoor set-up		No
With cable entry		No