



**Vertical partition, main busbar, HxW=350x800mm**

**Part no. XTPZBAVP2-H350W800  
178382**

| General specifications     |  |  |
|----------------------------|--|--|
| Product name               |  | Eaton xEnergy Main LV switchgear             |
| Part no.                   |  | XTPZBAVP2-H350W800                           |
| EAN                        |  | 4015081736850                                |
| Product Length/Depth       |  | 33.5 millimetre                              |
| Product height             |  | 298 millimetre                               |
| Product width              |  | 740 millimetre                               |
| Product weight             |  | 2.732 kilogram                               |
| Compliances                |  | RoHS conform                                 |
| Product Tradename          |  | xEnergy Main                                 |
| Product Type               |  | LV switchgear                                |
| Product Sub Type           |  | None   |
| Public Consumption         |  | Yes  |
| PDH Status                 |  | Active                                       |
| Product Family Description |  | ES-PMCC-PDC-Eaton xEnergy Main LV switchgear |
| Globally Marketable        |  | Yes  |

## Technical data ETIM 9.0

|  |  |    |                 |
|--|--|----|-----------------|
| Cabinet enclosures (EG000011) / Divider panel (enclosure/cabinet) (EC002525)   |  |    |                 |
| Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Panel (electrical cabinet) / Divider panel (electrical cabinet) (ecl@ss13-27-18-21-02 [AKE424019]) |  |    |                 |
| Modular spacing  |  | mm | 12.5            |
| Suitable for enclosure building width  |  | mm | 800             |
| Suitable for enclosure building depth  |  | mm | 800             |
| Width  |  | mm | 740             |
| Height   |  | mm | 298             |
| Material   |  |    | Steel           |
| Surface finishing  |  |    | Galvanized      |
| Colour   |  |    | Stainless steel |
| RAL-number   |  |    | 0               |
| With cable entry   |  |    | No              |
| Number of height units   |  |    | 0               |
| With lock  |  |    | No              |
| Construction type  |  |    | Individual part |
| For internal separation form 2a  |  |    | Yes             |
| For internal separation form 2b  |  |    | Yes             |
| For internal separation form 3a  |  |    | Yes             |
| For internal separation form 3b  |  |    | Yes             |
| For internal separation form 4a  |  |    | Yes             |
| For internal separation form 4b  |  |    | Yes             |