



Partition between two sections, XW, HxD = 300 x 800 mm

Part no. **XTPPSSZ-H300**
178384

General specifications		
Product name		Eaton xEnergy Main LV switchgear
Part no.		XTPPSSZ-H300
EAN		4015081736874
Product Length/Depth		482 millimetre
Product height		300.5 millimetre
Product width		35 millimetre
Product weight		3.137 kilogram
Compliances		RoHS conform
Product Tradename		xEnergy Main
Product Type		LV switchgear
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton xEnergy Main LV switchgear
Globally Marketable		Yes

Technical data ETIM 9.0

Cabinet enclosures (EG000011) / Divider panel (enclosure/cabinet) (EC002525)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Panel (electrical cabinet) / Divider panel (electrical cabinet) (ecl@ss13-27-18-21-02 [AKE424019])		
Modular spacing	mm	12.5
Suitable for enclosure building width	mm	0
Suitable for enclosure building depth	mm	800
Width	mm	35
Height	mm	300.5
Material		Steel
Surface finishing		Galvanized
Colour		Stainless steel
RAL-number		0
With cable entry		No
Number of height units		0
With lock		No
Construction type		Individual part
For internal separation form 2a		Yes
For internal separation form 2b		Yes
For internal separation form 3a		Yes
For internal separation form 3b		Yes
For internal separation form 4a		Yes
For internal separation form 4b		Yes