



Partition, NZM4/Main busbar area, horizontal, W=425mm

**Part no. XTPPN4BH-W425
180736**

General specifications		
Product name		Eaton xEnergy Main LV switchgear
Part no.		XTPPN4BH-W425
EAN		4015081759019
Product Length/Depth		642 millimetre
Product height		27 millimetre
Product width		335 millimetre
Product weight		1.23 kilogram
Compliances		RoHS conform
Product Tradename		xEnergy Main
Product Type		LV switchgear
Product Sub Type		None
Public Consumption		Yes
PDH Status		Active
Product Family Description		ES-PMCC-PDC-Eaton xEnergy Main LV switchgear
Globally Marketable		Yes

Technical data ETIM 9.0

Cabinet enclosures (EG000011) / Divider panel (enclosure/cabinet) (EC002525)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Panel (electrical cabinet) / Divider panel (electrical cabinet) (ecl@ss13-27-18-21-02 [AKE424019])		
Modular spacing	mm	12.5
Suitable for enclosure building width	mm	425
Suitable for enclosure building depth	mm	800
Width	mm	335
Height	mm	27
Material		Steel
Surface finishing		Galvanized
Colour		Stainless steel
RAL-number		0
With cable entry		No
Number of height units		0
With lock		No
Construction type		Individual part
For internal separation form 2a		No
For internal separation form 2b		Yes
For internal separation form 3a		No
For internal separation form 3b		Yes
For internal separation form 4a		No
For internal separation form 4b		Yes