



Adjustable thermostat, changeover contact

**Part no. NWS-TH/ESB/WK
255419**

General specifications		
Product name		Eaton Distribution parts
Part no.		NWS-TH/ESB/WK
EAN		4015082554194
Product Length/Depth		38 millimetre
Product height		67 millimetre
Product width		50 millimetre
Product weight		0.105 kilogram
Compliances		RoHS conform CE Marked
Product Tradename		None
Product Type		Distribution parts
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton Distribution parts
Globally Marketable		Yes
Product Specification Details		
Adjustment range temperature - max		60 °C
Adjustment range temperature - min		0 °C
Nominal current		16 A
Rated operational voltage (Ue) - max		230 V
Switch function type		Change-over contact

Technical data ETIM 8.0

Cabinet enclosures (EG000011) / Thermostat/hygrostat (switchgear cabinet) (EC004587)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Electrical cabinet air conditioning / Switchgear cabinet air conditioning (unspecified) (ecI@ss10.0.1-27-18-07-90 [BAC196011])		
Model		
Rated voltage	V	230
Rated current In	A	16
Adjustable setting value for relative air humidity	%	
Temperature setting range	°C	0 - 60
Mounting method		Screw mounting
Type of switch function		
With digital indication		No