



19-inch 7-gang socket outlet strip

Part no. NWS-STL/19/7F/UTE
Catalog No. 290031

Technical data ETIM 7.0

Domestic switching devices (EG000013) / Multiple socket (EC000330)			
Electric engineering, automation, process control engineering / Electrical installation, device / Low-voltage distribution system (mobile) / Socket outlet strip (ecl@ss10.0.1-27-14-26-04 [AFZ849015])			
Housing shape			Rectangular
Number of socket outlets with protective contact			7
Number of Euro socket outlets			0
Number of CEE socket outlets			0
Number of socket outlets with earth pin			0
Number of cold device socket outlets			0
Number of socket outlets type Bipasso (Italy)			0
Number of socket outlets Type P11 (Italy)			0
number of socket outlets Type P17 (Italy)			0
Number of NEMA-outlets			0
number of socket outlets swiss standard type 13			0
number of socket outlets swiss standard type 15			0
number of socket outlets swiss standard type 23			0
number of socket outlets swiss standard type 25			0
With on/off switch			No
Residual current circuit breaker (RCCB)			No
Number of universal multi standard sockets			0
Mains filter			No
Number of other socket outlets			0
Number of USB connections			0
Over voltage protection			No
Nominal current		A	16
Core cross section		mm ²	16
With cover			No
Material			Metal
Material quality			Aluminium
Halogen free			No
Surface protection			Anodised
Surface finishing			Matt
Colour			Aluminium
RAL-number (akin)			0
Transparent			No
Degree of protection (IP)			IP20
Length of power cord		m	2
Rotated central insert			No
Angle rotated central insert			35°
NEMA designation			