



**Cable grommet, PG16, IP65**

**Part no. KT16**  
**Catalog No. 022031**

**EL-Nummer 4132342**  
**(Norway)**

**Delivery program**

Product range			General switchboard accessories
Accessories			Cable management
Accessories			Cable grommets
For use with			For wall thickness 2 - 8 mm
Material			Soft PVC cadmium- and lead-free
Surface finish			similar RAL 7035
Cable entry			PG 16
Hole diameter		mm	23,5
Outer cable diameter		mm	7 - 17
Example of application: NYM/NYY cable, 4-core		mm <sup>2</sup>	1,5 - 10

**Technical data**

**Material characteristics**

Material			Soft PVC cadmium- and lead-free
----------	--	--	------------------------------------

**Technical data ETIM 7.0**

Cable and wire entry systems (EG000009) / Cable entry sleeve (EC000879)			
Electric engineering, automation, process control engineering / Electrical installation, device / Connection devices / Feed through spout (ecl@ss10.0.1-27-14-44-21 [AD1139007])			
Model			Closed
Insert for cable gland			No
Cable entry			Round
Number of cables			1 - 1
Suitable for cable diameter		mm	7 - 17
Bore diameter		mm	23.5
For wall thickness		mm	2 - 8
Thread size (metric)			0
Thread size PG			16
Total length		mm	0
With strain relief			No
Shrink technique			No
Angle model			No
Material			Plastic
Material quality			Polyvinyl chloride (PVC)
Surface protection			Other
Halogen free			No
Colour			Grey
Gastight			Yes
Fire resistant			No
Watertight			Yes
Degree of protection (IP)			IP65
Working temperature		°C	-5 - 40

## Dimensions

