



Прокладка , PG16 , IP65

Тип **КТ16**
Каталог № **022031**

Программа поставок

Ассортимент			Общие принадлежности к двери распределительного шкафа
Принадлежности			Управление кабелями
Принадлежности			Защитные кабельные чехлы
Применяемое для			Для стенок толщиной 2 - 8 мм
Материал			Пластифицированный ПВХ без содержания кадмия и свинца
Качество поверхности			как RAL 7035
ввод проводки			PG 16
Диаметр отверстия		мм	23,5
Наружный диаметр провода		мм	7 - 17
Применение кабеля NYM/NYY, 4#жильный		мм ²	1,5 - 10

Технические характеристики

материал

Материал			Пластифицированный ПВХ без содержания кадмия и свинца
----------	--	--	---

Технические характеристики согласно ETIM 7.0

Cable and wire entry systems (EG000009) / Cable entry sleeve (EC000879)			
Электротехника, электроника, системы автоматизации / Электроустановки, электромонтажные материалы / Connection devices / Feed through spout (ecl@ss10.0.1-27-14-44-21 [ADI139007])			
Model			Closed
Insert for cable gland			No
Cable entry			Round
Number of cables			1 - 1
Suitable for cable diameter		мм	7 - 17
Bore diameter		мм	23.5
For wall thickness		мм	2 - 8
Thread size (metric)			0
Thread size PG			16
Total length		мм	0
With strain relief			No
Shrink technique			No
Angle model			No
Material			Plastic
Material quality			Polyvinyl chloride (PVC)
Surface protection			Other
Halogen free			No
Colour			Grey
Gastight			Yes
Fire resistant			No
Watertight			Yes
Degree of protection (IP)			IP65
Working temperature		°C	-5 - 40

Размеры

