



Kabelová průchodka, PG36

Typ **KT36**  
 Catalog No. **033896**

### Dodavatelský program

Product range			General switchboard accessories
Příslušenství			uspořádání kabelů
Příslušenství			Kabelové průchodky
Použitelné pro			For wall thickness 2 - 8 mm
Materiál			Měkké PVC bez obsahu kadmia a olova
Vlastnosti povrchu			podobné RAL 7035
Vstup pro kabel			PG 36
Hole diameter		mm	48
Vnější průměr vedení		mm	18 - 40
Example of application: NYM/NYY cable, 4-core		mm <sup>2</sup>	10 - 70

### Technická data

#### Materiál

Materiál			Měkké PVC bez obsahu kadmia a olova
----------	--	--	----------------------------------------

### Technická data podle ETIM 7.0

Cable and wire entry systems (EG000009) / Cable entry sleeve (EC000879)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Connection devices / Feed through spout (ecl@ss10.0.1-27-14-44-21 [AD1139007])			
Model			Closed
Insert for cable gland			No
Cable entry			Round
Number of cables			1 - 1
Suitable for cable diameter		mm	18 - 40
Bore diameter		mm	48
For wall thickness		mm	2 - 8
Thread size (metric)			0
Thread size PG			36
Total length		mm	0
With strain relief			No
Shrink technique			No
Angle model			No
Material			Plastic
Material quality			Polyvinyl chloride (PVC)
Surface protection			Other
Halogen free			No
Colour			Grey
Gastight			Yes
Fire resistant			No
Watertight			Yes
Degree of protection (IP)			IP66
Working temperature		°C	-5 - 40

