



Cable grommet, PG36

Referencia **KT36**  
 Catalog No. **033896**

### Delivery program

Product range			General switchboard accessories
Accessories			Cable management
Accessories			Cable grommets
For use with			For wall thickness 2 - 8 mm
Material			Soft PVC cadmium- and lead-free
Surface finish			similar RAL 7035
Cable entry			PG 36
Hole diameter		mm	48
Outer cable diameter		mm	18 - 40
Example of application: NYM/NYY cable, 4-core		mm <sup>2</sup>	10 - 70

### Technical data

#### Material characteristics

Material			Soft PVC cadmium- and lead-free
----------	--	--	------------------------------------

### Technical data ETIM 7.0

Accesorios para la entrada de cables (EG000009) / Salida protectora de cables (EC000879)			
Tecnología electrónica, de automatización y de mando de procesos / Instalación eléctricas, equipo / Connection devices / Feed through spout (ecl@ss10.0.1-27-14-44-21 [AD1139007])			
Modelo			Cerrado
Entrada de cable			Redondo
Compatible con diámetro del cable desde/hasta		Millimeter	18 - 40
Diámetro de perforación		Millimeter	48
Para grosor de pared		Millimeter	2 - 8
Tamaño de la rosca, métrico (M..)			0
Tamaño de rosca PG			36
Longitud total		Millimeter	0
Disminución de tensión			No
Modelo del ángulo			No
Material			Plástico
Calidad de material			PVC
Tratamiento de superficie			Otros
Sin halógenos			No
Color			Gris
Estando			Si
Grado de protección (IP)			IP66
Intervalo de temperatura de funcionamiento		Degrees celsius	-5 - 40

## Dimensions

