



Fuse-link, high speed, 100 A, AC 690 V, DC 500 V, 200 kA, BS88, 18 x 96 mm, aR, BS, Special 80 mm fixing centres, thyristor fuse



Part no. 100A 690V TYPE T FUSE
Catalog No. 100AFE

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	100
Rated voltage			AC 690 V DC 500 V
Construction size			BS88
Size			18 x 96 mm
Utilization category			aR
Description			Special 80 mm fixing centres thyristor fuse
Breaking Capacity		kA	200
usable for size/applications			protection of DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			BS
Shape			offset bolted tags (slotted)
Standards/Regulations			BS88-4 IEC 60269-4

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			Other
Type of current			AC/DC
Rated voltage AC		V	690
Rated voltage DC		V	500
Rated current		A	100
Utilization category			aR (accompanied semiconductor protection)
Breaking capacity		kA	200
Colour code			None
Type of fuse status indicator			None
Power loss at rated current		W	23
Mounting holes			M8
Centre-to-centre distance of connections		mm	76