



Fuse-link, high speed, 100 A, AC 690 V, DC 500 V, 200 kA, BS88, 18 x 96 mm, aR, BS, Special 80 mm fixing centres, thyristor fuse



Part no. **100A 690V TYPE T FUSE**
 Catalog No. **100AFE**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	100
Rated voltage			AC 690 V DC 500 V
Construction size			BS88
Size			18 x 96 mm
Utilization category			aR
Description			Special 80 mm fixing centres thyristor fuse
Breaking Capacity		kA	200
usable for size/applications			protection of DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			BS
Shape			offset bolted tags (slotted)
Standards/Regulations			BS88-4 IEC 60269-4

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	100
Rated voltage		V	690
Voltage type			AC/DC
Rated switching capacity		kA	200
Utilization category			aR (accompanied semiconductor protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/4a317260-8e98-40d9-b43b-e80c53a102f6.pdf
-------------------------	---