









Leiteranschlussklemme, 1,5-16qmm, f. 5mm

Typ AKU16/5
Katalog Nr. 107187

Lieferprogramm

Sortiment			60-mm-System Compact-System
Grundfunktion			Anschluss- und Verbindungstechnik
Untersortiment			Universal-Leiteranschlussklemmen
Beschreibung			mit integrierter Haltefeder, geöffnetem Klemmraum und unverlierbarer Klemmschraube
Klemmraum B x H		mm	7.5 x 7.5
Breite		mm	11.5
Bemessungsbetriebsstrom	I_e	A	180
Leiter			1.5 - 16 mm ² AWG 14 - AWG 6. direkt geklemmt:    # 8 x 6 x 0.5 mm
verwendbar für			Alle 5 mm dicken Flachschielen

Hinweise

- Rundleiter eindrätig
-  Rundleiter feindrätig mit fachgerecht verpresster Aderendhülse
-  Rundleiter mehrdrätig
-  Sektorleiter eindrätig
-  Sektorleiter mehrdrätig
- # CU-Band
-  CU-Schiene

Approbationen

Product Standards			UL508A; CSA-C22.2 No. 14; IEC 60439-1; CE marking
UL File No.			E307559
UL Category Control No.			NMTR2, NMTR8
CSA File No.			236217
CSA Class No.			3211-37
North America Certification			UL recognized, CSA certified
Conditions of Acceptability			Refer to approbation report
Specially designed for North America			No
Suitable for			Feeder circuits
Current Limiting Circuit-Breaker			Refer to approbation report
Max. Voltage Rating			600 V AC
Degree of Protection			Feeder circuits

Abmessungen

