










**Leiteranschlussklemme, 16-70qmm, f. 5 mm**

**Typ** AKU70/5  
**Katalog Nr.** 107189

**Lieferprogramm**

Sortiment			60-mm-System Compact-System
Grundfunktion			Anschluss- und Verbindungstechnik
Untersortiment			Universal-Leiteranschlussklemmen
Beschreibung			mit integrierter Haltefeder, geöffnetem Klemmraum und unverlierbarer Klemmschraube
Klemmraum B x H		mm	14 x 14
Breite		mm	20.5
Bemessungsbetriebsstrom	$I_e$	A	400
Leiter			16 - 70 mm <sup>2</sup> AWG 4 - AWG 2/0. direkt geklemmt:   # 2x (3 x 9 x 0.8 mm) oder 6 x 9 x 0.8 mm
verwendbar für			Alle 5 mm dicken Flachschiene
<b>Hinweise</b>			
<input type="radio"/> Rundleiter eindrätig			
 Rundleiter feindrätig mit fachgerecht verpresster Aderendhülse			
 Rundleiter mehrdrätig			
 Sektorleiter eindrätig			
 Sektorleiter mehrdrätig			
# CU-Band			
 CU-Schiene			

**Approbationen**

Product Standards			UL508A; CSA-C22.2 No. 14; IEC 60439-1; CE marking
UL File No.			E307559
UL Category Control No.			NMTR2, NMTR8
CSA File No.			236217
CSA Class No.			3211-37
North America Certification			UL recognized, CSA certified
Conditions of Acceptability			Refer to approbation report
Specially designed for North America			No
Suitable for			Feeder circuits
Current Limiting Circuit-Breaker			Refer to approbation report
Max. Voltage Rating			600 V AC
Degree of Protection			Feeder circuits

## Abmessungen

