



Spreizklemme, 95-185qmm, für 20x5-30x10

Typ **AKS185**  
 Katalog Nr. **107195**

## Lieferprogramm

Sortiment			60-mm-System 185-mm-System
Grundfunktion			Anschluss- und Verbindungstechnik
Untersortiment			Spreizklemmen
Beschreibung			Bohrungslose Anschlussstechnik auf Sammelschienen Kontaktierung der Leitung mit der Sammelschiene erfolgt über Kabelbett
Breite		mm	38
Bemessungsbetriebsstrom	$I_e$	A	500
Leiter			95 - 185 mm <sup>2</sup> AWG3/0 - MCM350. direkt geklemmt:   
Cu-Zahl		kg	0,00
verwendbar für			20 x 5/10 25 x 5/10 30 x 5/10
verwendbar für			Doppel-T-Profil
<b>Hinweise</b>			
<input type="radio"/> Rundleiter eindrätig			
Rundleiter feindrätig mit fachgerecht verpresster Aderendhülse			
Rundleiter mehrdrätig			
Sektorleiter eindrätig			
Sektorleiter mehrdrätig			
# CU-Band			
<input checked="" type="checkbox"/> CU-Schiene			

## Approbationen

Product Standards			UL508A; CSA-C22.2 No. 14; IEC 60439-1; CE marking
UL File No.			E307559
UL Category Control No.			NMTR2, NMTR8
CSA File No.			236217
CSA Class No.			3211-37
North America Certification			UL recognized, CSA certified
Conditions of Acceptability			Refer to approbation report
Specially designed for North America			No
Suitable for			Feeder circuits
Current Limiting Circuit-Breaker			Refer to approbation report
Max. Voltage Rating			600 V AC
Degree of Protection			Feeder circuits

## Abmessungen

