



Partition, F, connection-/busbar back area, W=1200mm

**Part no.** XPFCB12

**Catalog No.** 110267

**EL-Nummer (Norway)** 2465760

**Technical data ETIM 8.0**

Cabinet enclosures (EG000011) / Divider panel (enclosure/cabinet) (EC002525)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Panel (electrical cabinet) / Divider panel (electrical cabinet) (ecl@ss10.0.1-27-18-21-02 [AKE424014])		
Modular spacing	mm	12.5
Suitable for enclosure building width	mm	1200
Suitable for enclosure building depth	mm	30
Width	mm	625
Height	mm	30
Material		Stainless steel
Surface finishing		Other
Colour		Stainless steel
RAL-number		0
With cable entry		No
Number of height units		0
With lock		No
Construction type		Assembly kit
For internal separation form 2a		Yes
For internal separation form 2b		Yes
For internal separation form 3a		Yes
For internal separation form 3b		Yes
For internal separation form 4a		Yes
For internal separation form 4b		Yes