

Front plate for HxW=125x1000mm, with 45 mm device cutout



Part no. BPZ-FP/MSW-1000/125-45
120789
EL Number 2461065
(Norway)

General specifications		
Product name		Eaton xEnergy Basic front plate
Part no.		BPZ-FP/MSW-1000/125-45
EAN		4015081186198
Product Length/Depth		35 millimetre
Product height		130 millimetre
Product width		925 millimetre
Product weight		1.13 kilogram
Compliances		RoHS conform
Product Tradename		xEnergy Basic
Product Type		Accessories
Product Sub Type		Front plate
Delivery program		
Type		Additional equipment
Color		Light gray (RAL 7035)
Technical Data - Mechanical		
Surface finishing		Powder coating With powder coating
Mounting method		Flush mounting Surface mounting Floor standing distribution board
Mounting position		Vertical Horizontal
Material		Sheet steel Steel
Number of height units		0
Number of module space units (total)		46
Number of rows		1
Front plate cutout size		45 mm
Housing material		Sheet steel
Suitable for enclosure building height		125 mm
Suitable for enclosure building width		1000 mm
Suitable for width		1000 mm
Additional information		
Functions		Additional equipment

Technical data ETIM 8.0

Cabinet enclosures (EG000011) / Front panel (enclosure/cabinet) (EC000456)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Elements for switching cabinet, housing, rack / Front plate (electrical cabinet) (ecl@ss10.0.1-27-18-28-06 [AKE465013])		
Width	mm	925
Height	mm	130
Suitable for enclosure building width	mm	1000
Suitable for enclosure building height	mm	125
Number of height units		0
Material		Steel
Surface finishing		Powder coating