



Base frame for WxD= 1200 x 300mm, grey

Part no. XLB1203

Catalog No. 132934

**EL-Nummer 2465490
(Norway)**

Technical data ETIM 8.0

Cabinet enclosures (EG000011) / Enclosure/cabinet (empty) (EC000261)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Electrical cabinet (empty) / Electrical cabinet (ecl@ss10.0.1-27-18-01-01 [AGZ056016])		
Width	mm	280
Height	mm	250
Depth	mm	1210
Material		Steel
Material quality		Other
Surface finishing		Powder coating
Colour		Grey
RAL-number		7035
Detached		No
Floor standing wall model		Yes
Suitable for wall mounting		No
Corner model		No
Intermediate mounting		No
Connectable		Yes
With mounting plate		No
Mounting plate depth-adjustable		Yes
Suitable for wall built-in		No
Pole fastening		No
Number of doors		0
Number of locks		0
Suitable for metrical mounting		Yes
Suitable for outdoor set-up		No
Pitched roof		No
EMC-version		Yes
With glazed door		No
With ventilation door		No
With backside door		No
Impact strength		IK10
Degree of protection (IP)		Other
Degree of protection (NEMA)		Other
Thermal dissipation (Delta T = 20 K) according to IEC/TR 60890	W	0
Max. permissible load of the enclosure according to IEC 62208	N	5000
Max. permissible load of the door(s) according to IEC 62208	N	1000
Max. permissible load of the mounting plate according to IEC 62208	N	4000