



Section door, closed IP55, left or right-hinged, HxW = 1600 x 425mm, grey



Powering Business Worldwide™

**Part no.** XLSD5S164

**Catalog No.** 132941

**EL-Nummer (Norway)** 2465378

### Technical data ETIM 8.0

Cabinet enclosures (EG000011) / Door/operating panel (enclosure/cabinet) (EC000747)			
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Door (electrical cabinet) / Door/operating panel (enclosure) (ecI@ss10.0.1-27-18-22-04 [ACN614011])			
Model			Stop door
Version as glazed door			No
Version as door for disconnecting switch interlocking			No
Width		mm	492.7
Height		mm	40
Depth		mm	1540
EMC-version			Yes
Material			Steel
Surface finishing			Powder coating
Colour			Grey
Degree of protection (IP)			IP55
Degree of protection (NEMA)			4X