



**Base frame for WxD= 850 x 300mm, grey**

**Part no. XLB08503**

**Catalog No. 143342**

**EL-Nummer 2465504  
(Norway)**

**Technical data ETIM 8.0**

Cabinet enclosures (EG000011) / Enclosure/cabinet (empty) (EC000261)			
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Electrical cabinet (empty) / Electrical cabinet (ecl@ss10.0.1-27-18-01-01 [AGZ056016])			
Width	mm		275
Height	mm		240
Depth	mm		850
Material			Steel
Material quality			Other
Surface finishing			Powder coating
Colour			Grey
RAL-number			7035
Detached			No
Floor standing wall model			Yes
Suitable for wall mounting			No
Corner model			No
Intermediate mounting			No
Connectable			Yes
With mounting plate			No
Mounting plate depth-adjustable			Yes
Suitable for wall built-in			No
Pole fastening			No
Number of doors			0
Number of locks			0
Suitable for metrical mounting			Yes
Suitable for outdoor set-up			No
Pitched roof			No
EMC-version			Yes
With glazed door			No
With ventilation door			No
With backside door			No
Impact strength			IK10
Degree of protection (IP)			Other
Degree of protection (NEMA)			Other
Thermal dissipation (Delta T = 20 K) according to IEC/TR 60890	W		0
Max. permissible load of the enclosure according to IEC 62208	N		5000
Max. permissible load of the door(s) according to IEC 62208	N		1000
Max. permissible load of the mounting plate according to IEC 62208	N		4000