



Тип
Каталог №

EPTV05
143862

Технические характеристики согласно ETIM 7.0

Cable carrying systems (EG000004) / Support/profile rail (EC000386)		
Электротехника, электроника, системы автоматизации / Электроизоляционные и контактные материалы / Cable carrier system / Shank/profile bar (ec1@ss10.0.1-27-40-05-01 [AC0321012])		
Length	mm	32
Width	mm	28.5
Height	mm	32
Slit width	mm	9.5
Material thickness	mm	2
Profile shape		U-profile
Model		Singular profile
Type of perforation		3 sides punched
Hole width	mm	3.6
With tothing		No
Snap-off		No
Load bearing capacity	kN	0
Area moment of inertia Iy	cm ⁴	0
Area of inertia Iz	cm ⁴	0
Moment of resistance Wy	cm ³	0
Moment of resistance Wz	cm ³	0
Suitable for circuit integrity		No
Material		Steel
Material quality		Other
Surface protection		Galvanic/electrolytic zinc plated
Colour		Other
RAL-number		0