



**Sikrings-lastbryter**

**Type** PIFT2L331C401CCAE  
**Catalog No.** 160256  
**Alternate Catalog No.** PIFT2L331C401CCAE

Illustrasjon lik

**Tekniske data etter ETIM 6.0**

Low-voltage industrial components (EG000017) / Fuse switch disconnecter (EC001040)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse switch disconnecter (ecl@ss8.1-27-37-14-01 [AKF058010])			
Version as main switch			No
Version as safety switch			No
Max. rated operation voltage Ue AC	V		690
Rated permanent current Iu	A		400
Rated operation power at AC-23, 400 V	kW		0
Conditioned rated short-circuit current Iq	kA		55
Rated short-time withstand current Icw	kA		0
Suitable for fuses			NH2
Number of poles			3
With error protection			Yes
Type of electrical connection of main circuit			Screw connection
Suitable for ground mounting			No
Suitable for front mounting 4-hole			No
Suitable for busbar mounting			Yes
Type of control element			Door coupling rotary drive
Position control element			Front side
Motor drive optional			No
Motor drive integrated			No
Version as emergency stop installation			No
Degree of protection (IP), front side			IP40

**Mer produktinformasjon (forbindelser)**

Instruction leaflet PIFT	<a href="https://es-assets.eaton.com/ENGINEERING/CONFIGURATOR/XENERGY/IL/IL-PIFT-01M-2018-08.pdf">https://es-assets.eaton.com/ENGINEERING/CONFIGURATOR/XENERGY/IL/IL-PIFT-01M-2018-08.pdf</a>
--------------------------	---