

**Tipo** PIFT3L300CE  
**Catalog No.** 161581  
**Alternate Catalog No.** PIFT3L300CE

Abbildung ähnlich

## Dati tecnici secondo ETIM 6.0

Low-voltage industrial components (EG000017) / Fuse switch disconnecter (EC001040)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse switch disconnecter (ecl@ss8.1-27-37-14-01 [AKF058010])			
Version as main switch			No
Version as safety switch			No
Max. rated operation voltage Ue AC		V	690
Rated permanent current Iu		A	630
Rated operation power at AC-23, 400 V		kW	0
Conditioned rated short-circuit current Iq		kA	55
Rated short-time withstand current Icw		kA	0
Suitable for fuses			NH3
Number of poles			3
With error protection			Yes
Type of electrical connection of main circuit			Screw connection
Suitable for ground mounting			No
Suitable for front mounting 4-hole			No
Suitable for busbar mounting			Yes
Type of control element			Door coupling rotary drive
Position control element			Front side
Motor drive optional			No
Motor drive integrated			No
Version as emergency stop installation			No
Degree of protection (IP), front side			IP40

## Ulteriori informazioni sul prodotto (link)

Libretto di istruzioni PIFT	<a href="https://es-assets.eaton.com/ENGINEERING/CONFIGURATOR/XENERGY/IL/IL-PIFT-01M-2018-08.pdf">https://es-assets.eaton.com/ENGINEERING/CONFIGURATOR/XENERGY/IL/IL-PIFT-01M-2018-08.pdf</a>
-----------------------------	---