



Series connection time switch 24 hrs., series connection time switch, 1 TLE



Part no. TSSD1N0
Catalog No. 167389
Alternate Catalog No. TSSD1N0

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I_n	A	0
Heat dissipation per pole, current-dependent	P_{vid}	W	0
Equipment heat dissipation, current-dependent	P_{vid}	W	0
Static heat dissipation, non-current-dependent	P_{vs}	W	0.9
Heat dissipation capacity	P_{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	50
			0

Technical data ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Analogous time switch for distribution board (EC002304)			
Electric engineering, automation, process control engineering / Measurement technology, process measurement technology / Measuring appliance, time / Analogous time switch (ecI@ss10.0.1-27-20-01-09 [ACN651011])			
Mounting method			DIN rail
Number of channels			1
Supply voltage		V	230 - 230
Voltage type of supply voltage			AC
Frequency supply voltage		Hz	50 - 50
Autonomy in hours			0
Autonomy in years			0
Accuracy per day		s	0
60 min. program			No
24 h program			Yes
Weekly program			No
Annual program			No
Mains synchronous			Yes
Quartz controlled			Yes
Contact type			Normally open contact
Shortest switching time channel 1		min	15
Shortest switching time channel 2		min	0
Program shift divide 1		min	15
Program shift divide 2		min	0
Automatic switching summer-/winter time			No
Manual operation			Yes
Switching preselection			Yes
Nominal switching current at 250 V AC		A	16
Potential free switch contact			Yes
Degree of protection (IP)			IP20
Width in number of modular spacings			1
Width		mm	17.5
Height		mm	90
Depth		mm	65.5

