



Fuse-link, high speed, 160 A, DC 750 V, 100 kA, compact size 1, gR, IEC, type K indicator

Part no. FUSE 160A 750V 1*BKN/130 GR DC
 Catalog No. 170E3581

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	160
Rated voltage			DC 750 V
Construction size			compact size 1
Utilization category			gR
Status indicator			type K indicator
Breaking Capacity		kA	100
usable for size/applications			traction
Standard/Approval			IEC
Shape			square body with flush end contacts
Standards/Regulations			IEC 60269-4

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			Other
Type of current			DC
Rated voltage AC		V	
Rated voltage DC		V	750
Rated current		A	160
Utilization category			gR (general purpose semiconductor protection)
Breaking capacity		kA	0.1
Colour code			None
Type of fuse status indicator			Other
Power loss at rated current		W	26
Mounting holes			M8
Centre-to-centre distance of connections		mm	3276.59997837444401427

Additional product information (links)

Product datasheet (pdf)	http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/Catalogs/BUS_Ele_SB_DC_Fuses_750Vdc_63_500A.pdf
-------------------------	---