



Fuse-link, high speed, 100 A, AC 690 V, 200 kA, size 000, 24 x 36 x 96 mm, aR, IEC, visual indicator



Part no. FUSE 100A 690V 000F/70 AR UR
 Catalog No. 170M1517

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	100
Rated voltage			AC 690 V
Construction size			size 000
Size			24 x 36 x 96 mm
Utilization category			aR
Status indicator			visual indicator
Breaking Capacity		kA	200
usable for size/applications			semiconductor protection
Standard/Approval			IEC
Shape			square body with offset bolted tags
Standards/Regulations			IEC 60269-4

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			000
Type of current			AC
Rated voltage AC		V	690
Rated voltage DC		V	
Rated current		A	100
Utilization category			aR (accompanied semiconductor protection)
Breaking capacity		kA	200
Colour code			None
Type of fuse status indicator			Top fuse status indicator
Power loss at rated current		W	
Mounting holes			M8
Centre-to-centre distance of connections		mm	73.8

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusssmann.com/pdf/4a317260-8e98-40d9-b43b-e80c53a102f6.pdf
-------------------------	---