



Fuse-link, high speed, 20 A, DC 2000 V, 100 kA, 39 x 66 x 216 mm, aR, IEC, type K indicator



Part no. FUSE 20A 2000VDC 1C/A170 SST AR
Catalog No. 170M2046

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	20
Rated voltage			DC 2000 V
Size			39 x 66 x 216 mm
Utilization category			aR
Status indicator			type K indicator
Breaking Capacity		kA	100
usable for size/applications			traction third rail
Standard/Approval			IEC
Shape			square body with offset bolted tags
Standards/Regulations			IEC 60269-4

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			1
Type of current			DC
Rated voltage AC		V	
Rated voltage DC		V	2000
Rated current		A	20
Utilization category			aR (accompanied semiconductor protection)
Breaking capacity		kA	0
Colour code			None
Type of fuse status indicator			Other
Power loss at rated current		W	
Mounting holes			M8
Centre-to-centre distance of connections		mm	197

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/bc63d969-3074-40f0-ae38-6a553cc29762.pdf
-------------------------	---