



**Base frame for WxD= 650 x 400mm, grey**

**Part no. XLB06504**

**Catalog No. 174270**

**EL-Nummer 2455646  
(Norway)**



Powering Business Worldwide™

**Technical data ETIM 8.0**

Cabinet enclosures (EG000011) / Enclosure/cabinet (empty) (EC000261)			
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Electrical cabinet (empty) / Electrical cabinet (ecl@ss10.0.1-27-18-01-01 [AGZ056016])			
Width	mm	651	
Height	mm	240	
Depth	mm	376	
Material		Steel	
Material quality		Other	
Surface finishing		Powder coating	
Colour		Grey	
RAL-number		7035	
Detached		No	
Floor standing wall model		Yes	
Suitable for wall mounting		No	
Corner model		No	
Intermediate mounting		No	
Connectable		Yes	
With mounting plate		No	
Mounting plate depth-adjustable		Yes	
Suitable for wall built-in		No	
Pole fastening		No	
Number of doors		0	
Number of locks		0	
Suitable for metrical mounting		Yes	
Suitable for outdoor set-up		No	
Pitched roof		No	
EMC-version		Yes	
With glazed door		No	
With ventilation door		No	
With backside door		No	
Impact strength		IK10	
Degree of protection (IP)		Other	
Degree of protection (NEMA)		Other	
Thermal dissipation (Delta T = 20 K) according to IEC/TR 60890	W	0	
Max. permissible load of the enclosure according to IEC 62208	N	5000	
Max. permissible load of the door(s) according to IEC 62208	N	1000	
Max. permissible load of the mounting plate according to IEC 62208	N	4000	