



Switch, 10A, 2G, 2-way, stainless steel

Part no. **B022SS**
 Catalog No. **B022SS**

Delivery program

Product Range			Copa Fix
Function			Switches
Current rating	Amperage		10 AX (100 Watt Self Ballasted Lamp(s) (SBL))
Rated operating voltage	Volts		250V~
No. of gang			2 Gang
Switch type			2 Way
Types conform to (Standards)			BS EN 60669-2-1 BS EN 60669-1 IEC 60669-2-1 IEC 60669-1
Front plate colour			Stainless Steel
Front plate material			Stainless Steel
Rocker colour			White
Rocker material			Urea
Base colour			Grey
Base material			Thermoplastic
Front plate / module dimensions		mm	87 x 87
Front plate depth		mm	5.8
Fixing Centres		mm	60.3
Recommended Minimum back box depth		mm	25
Weight (kgs)		kgs	0.099
Contact material			Silver Nickel
Terminal material			Brass
Terminal Screw Details			Zinc Coated Steel with clear Passivation
Terminal capacity (L.N & E)		mm ²	4 x 1.5mm ² or 2 x 2.5mm ² or 1 x 4.0mm ²
Terminal screw head design			Combination Head
IP Rating			IP20
Finish / Color			Stainless Steel

Technical data ETIM 8.0

Domestic switching devices (EG000013) / Installation switch (EC001590)			
Electric engineering, automation, process control engineering / Electrical installation, device / Installation switch set / Switch (ecl@ss10.0.1-27-14-40-53 [ACN451011])			
Wiring system			Two-way switch
Method of operation			Rocker/button
Assembly arrangement			Basic element with full cover plate
Number of modules (module system)			0
Push button switch			Yes
Number of rockers			2
Mounting method			Flush mounted (plaster)
Type of fastening			Screw mounting
With mounting plate			
Material			Metal
Material quality			Stainless steel
Halogen free			Yes
Anti-bacterial treatment			
Surface protection			Lacquered

Surface finishing			Matt
Colour			Stainless steel
RAL-number (similar)			0
Label space/information surface			No
Illumination			
Function lighting			Illuminated (on)
Type of lighting			
Suitable for degree of protection (IP)			IP3X
Impact strength			
Nominal voltage		V	240
Rated current		A	10
Switching current for fluorescent lamps		AX	10
Feedback-signal contact			No
Connection type			Screwed terminal
Heating switch			
Washing machine switch			No
Width of device		mm	86
Height of device		mm	86
Depth of device		mm	35
Built-in depth		mm	25
Compatible with Apple HomeKit			
Compatible with Google Assistant			
Min. depth of built-in installation box		mm	25
Compatible with Amazon Alexa			
IFTTT support available			