



Socket outlet, 13A, 2G, unswitched, stainless steel

Part no. **B112SS**
 Catalog No. **B112SS**

Delivery program

| | | | |
|------------------------------------|----------|-----------------|--|
| Product Range | | | Copa Fix |
| Function | | | Sockets |
| Current rating | Amperage | | 13 A |
| Rated operating voltage | Volts | | 250V~ |
| No. of gang | | | 2 Gang |
| Types conform to (Standards) | | | BS 1363-2 |
| Front plate colour | | | Stainless Steel |
| Front plate material | | | Stainless Steel |
| Base colour | | | Grey |
| Base material | | | Thermoplastic |
| Front plate / module dimensions | | mm | 148 x 87 |
| Front plate depth | | mm | 5.8 |
| Fixing Centres | | mm | 120.6 |
| Recommended Minimum back box depth | | mm | 25 |
| Weight (kgs) | | kgs | 0.139 |
| Contact material | | | Silver Nickel |
| Terminal material | | | Brass |
| Terminal Screw Details | | | Zinc Coated Steel with clear Passivation |
| Terminal capacity (L.N & E) | | mm ² | L, N & E in Base = 2 x 4.0mm ² or 1 x 6.0mm ² Earth on Strap = 1 x 4.0mm ² or 1 x 6.0mm ² |
| Terminal screw head design | | | Combination Head |
| IP Rating | | | IP20 |
| Finish / Color | | | Stainless Steel |