



Connection unit, 13A, unswitched, neon, stainless steel

Part no. **B220NSS**
 Catalog No. **B220NSS**

Delivery program

Product Range			Copa Fix
Function			Connection Units
Current rating	Amperage		13 A
Rated operating voltage	Volts		250V~
No. of gang			1 Gang
Types conform to (Standards)			BS 1363-4
Front plate colour			Stainless Steel
Front plate material			Stainless Steel
Base colour			Grey
Base material			Thermoplastic
Front plate / module dimensions		mm	87 x 87
Front plate depth		mm	5.8
Fixing Centres		mm	60.3
Recommended Minimum back box depth		mm	25
Weight (kgs)		kgs	0.101
Contact material			Silver Nickel
Terminal material			Brass
Terminal Screw Details			Zinc Coated Steel with clear Passivation
Terminal capacity (L.N & E)		mm ²	4 x 2.5mm ² or 2 x 4.0mm ²
Terminal screw head design			Combination Head
IP Rating			IP20
Finish / Color			Stainless Steel

Technical data ETIM 8.0

Domestic switching devices (EG000013) / Appliance connector (EC003546)			
Electric engineering, automation, process control engineering / Electrical installation, device / Installation switch set / Installation switch set (unspecified) (ecl@ss10.0.1-27-14-40-90 [AGZ584015])			
Nominal current		A	
Colour			Grey
Model			
Standard			