



Shaver socket, 230V/115V AC, stainless steel

Part no. **B370SS**
 Catalog No. **B370SS**

Delivery program

Product Range			Copa Fix
Function			Other Accessories
Current rating	Amperage		20 VA
Rated operating voltage	Volts		230V~
No. of gang			1 Gang
Types conform to (Standards)			BS EN 61558-1 BS EN 61558-2-5 IEC 61558-1 IEC 61558-2-5
Front plate colour			Stainless Steel
Front plate material			Stainless Steel
Base colour			Brown
Base material			Urea
Front plate / module dimensions		mm	148 x 87
Front plate depth		mm	5.8
Fixing Centres		mm	120.6
Recommended Minimum back box depth		mm	47
Weight (kgs)		kgs	0.68
Contact material			Silver Nickel
Terminal material			Brass
Terminal Screw Details			Zinc Coated Steel with clear Passivation
Terminal capacity (L.N & E)		mm ²	L + N = 3 x 1.0mm ² 2 x 1.5mm ² or 1 x 2.5mm ² - E = 6 x 1.0mm ² or 4 x 1.5mm ²
Terminal screw head design			Combination Head
IP Rating			IP20
Finish / Color			Stainless Steel

Technical data ETIM 8.0

Domestic switching devices (EG000013) / Razor socket outlet (EC000186)			
Electric engineering, automation, process control engineering / Electrical installation, device / Installation switch set / Electric razor socket (ecl@ss10.0.1-27-14-40-36 [AKE347013])			
Assembly arrangement			Basic element with central cover plate
Number of modules (module system)			0
Mounting method			Flush mounted (plaster)
With hinged lid			
Voltage reversible			Yes
Nominal voltage low value		V	110
Nominal voltage high value		V	240
Material			Metal
Material quality			Stainless steel
Halogen free			Yes
Surface protection			Lacquered
Surface finishing			Matt
Colour			Stainless steel

RAL-number (similar)		0
Transparent		
Amperage	A	2
Width of device	mm	86
Height of device	mm	146
Depth of device	mm	50
With built-in installation box		
Min. depth of built-in installation box	mm	47