


**Typ
Catalog No.**
**B391SS
B391SS**

Dodavatelský program

| | | | |
|------------------------------------|--|-----|-------------------|
| Product Range | | | Copa Fix |
| Function | | | Other Accessories |
| No. of gang | | | 1 Gang |
| Types conform to (Standards) | | | BS 5773 |
| Front plate colour | | | Stainless Steel |
| Front plate material | | | Stainless Steel |
| Front plate / module dimensions | | mm | 87 x 87 |
| Front plate depth | | mm | 5.8 |
| Fixing Centres | | mm | 60.3 |
| Recommended Minimum back box depth | | mm | 25 |
| Weight (kgs) | | kgs | 0.091 |
| Povrch / barva | | | Nerezová ocel |

Technická data podle ETIM 8.0

| | | | |
|---|--|----|-----------------|
| Domestic switching devices (EG000013) / Cover frame for domestic switching devices (EC000007) | | | |
| Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalací zařízení, přístroj / Instalací vypínacová program / Zakrývací rám (ecl@ss10.0.1-27-14-40-01 [AAB932014]) | | | |
| Number of units | | | 1 |
| Mounting direction | | | Horizontal |
| Number of units horizontal | | | 0 |
| Number of units vertical | | | 0 |
| Number of modules horizontal (module system) | | | 0 |
| Number of modules vertical (module system) | | | 0 |
| Number of switch inserts | | | 1 |
| With mounting grid | | | No |
| Flush-mounted installation | | | Yes |
| Suitable for floor box | | | |
| Suitable for wall duct | | | |
| Suitable for built-in installation | | | Yes |
| Label space/information surface | | | |
| Material | | | Metal |
| Material quality | | | Stainless steel |
| Halogen free | | | Yes |
| Anti-bacterial treatment | | | |
| Surface protection | | | Lacquered |
| Surface finishing | | | Matt |
| Colour | | | Stainless steel |
| RAL-number (similar) | | | 0 |
| Transparent | | | |
| With hinged lid | | | |
| Degree of protection (IP) | | | IP3X |
| Impact strength | | | |
| Type of fastening | | | Screw mounting |
| Width | | mm | 90 |
| Height | | mm | 20 |
| Depth | | mm | 90 |
| Built-in width | | mm | 86 |
| Built-in height | | mm | 86 |
| Diameter bore hole (opening) | | mm | 0 |

