



Metal plate, stainless steel

Part no. CM692SS
Catalog No. CM692SS

Delivery program

Product Range			Copa
Function			Cover Plates Options
No. of gang			2 Gang
Front plate colour			Stainless Steel
Front plate material			Stainless Steel
Front plate / module dimensions		mm	147 x 86
Front plate depth		mm	5.8
Weight (kgs)		kgs	0.048
Finish / Color			Stainless Steel

Technical data ETIM 8.0

Domestic switching devices (EG000013) / Cover frame for domestic switching devices (EC000007)			
Electric engineering, automation, process control engineering / Electrical installation, device / Installation switch set / Cover frame (ecl@ss10.0.1-27-14-40-01 [AAB932014])			
Number of units			1
Mounting direction			Horizontal
Number of units horizontal			0
Number of units vertical			0
Number of modules horizontal (module system)			0
Number of modules vertical (module system)			0
Number of switch inserts			0
With mounting grid			No
Flush-mounted installation			Yes
Suitable for floor box			
Suitable for wall duct			
Suitable for built-in installation			Yes
Label space/information surface			
Material			Metal
Material quality			Stainless steel
Halogen free			Yes
Anti-bacterial treatment			
Surface protection			Lacquered
Surface finishing			Matt
Colour			Stainless steel
RAL-number (similar)			0
Transparent			
With hinged lid			
Degree of protection (IP)			IP3X
Impact strength			
Type of fastening			Engage (snap)
Width		mm	10
Height		mm	100
Depth		mm	150
Built-in width		mm	148
Built-in height		mm	86
Diameter bore hole (opening)		mm	0