




Continuous light, white

Part no. SL-L-W
Catalog No. 205312
Alternate Catalog No. SL-L-W

Delivery program

Product range			SL signal towers
Single unit/Complete unit			Element
Degree of Protection			IP54
Description			without light elements
Colour			white
			
Connection to SmartWire-DT			no

Technical data

General			
Degree of protection, IEC/EN 60529			IP54

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	55

Technical data ETIM 5.0

Low-voltage industrial components (EG000017) / Optical module for signal tower (EC000232)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Optical module for signal tower (ecl@ss8-27-37-12-20 [AKF038010])			
Function			Continuous light
Colour			Clear
Outer diameter		mm	58
Degree of protection (IP)			IP54
Operating voltage at AC 50 Hz		V	230 - 230
Operating voltage at AC 60 Hz		V	230 - 230
Operating voltage at DC		V	24 - 24
Voltage type			AC/DC
Type of lamp			None
Colour housing			-

Approvals

Product Standards			IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			012528
CSA Class No.			3211-03
North America Certification			UL listed, CSA certified

Dimensions

