




Światło pulsujące, 130VAC, zielony

Typ **SL-BL130-G**
 Catalog No. **205324**
 Alternate Catalog No. **SL-BL130-G**

Program dostaw

Asortyment			Kolumny sygnalizacyjne SL
Stopień ochrony			IP54
Pojedyncze urządzenie / kompletne urządzenie			Moduł
Opis			Bez źródła światła Częstotliwość f ~ 1 Hz
Znamionowe napięcie pracy	U_e	V	110 - 130 V AC
Kolor			
Podłączanie do SmartWire-DT			nie

Świadectwo typu zgodnie z IEC/EN 61439

Dane techniczne dla zaświadczenia rodzaju konstrukcji			
Robocza temperatura otoczenia min.		°C	-25
Robocza temperatura otoczenia maks.		°C	55

Dane techniczne zgodne z ETIM 5.0

Low-voltage industrial components (EG000017) / Optical module for signal tower (EC000232)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Optical module for signal tower (ecl@ss8-27-37-12-20 [AKF038010])			
Function			Blinker light
Colour			Green
Outer diameter		mm	58
Degree of protection (IP)			IP54
Operating voltage at AC 50 Hz		V	130 - 130
Operating voltage at AC 60 Hz		V	130 - 130
Operating voltage at DC		V	0 - 0
Voltage type			AC
Type of lamp			None
Colour housing			-

Aprobaty

Product Standards			IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			012528
CSA Class No.			3211-03
North America Certification			UL listed, CSA certified

