



Опорная стойка; + труба 250 мм

**Тип** SL-F250  
**Каталог №** 205346  
**Alternate Catalog No.** SL-F250

### Программа поставок

Ассортимент			Световые сигнальные башни SL
Отдельное устройство/законченное устройство			Отдельное устройство
Длина		мм	250
Материал			Черный пластик
Подключение к SmartWire-DT			нет

### Bauartnachweis nach IEC/EN 61439

Технические характеристики для подтверждения типа конструкции			
Мин. рабочая температура		°C	-25
Макс. рабочая температура		°C	55

### Технические характеристики согласно ETIM 5.0

Low-voltage industrial components (EG000017) / Stand for signal tower with tube (EC001259)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Signal column element, foot with pipe (ecl@ss8-27-37-12-34 [AKF052010])			
Colour			Black
Tube length		mm	250
Material			Plastic

### Апробации

Product Standards			IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			012528
CSA Class No.			3211-03
North America Certification			UL listed, CSA certified

## Размеры

