

DATASHEET - 46KV 1A REMOVABLE B/H EXPULSION LINK



Expulsion fuse-link, medium voltage, 1 A, AC 46 kV, 8 kA, 787 mm, ANSI, removable NEMA button head link, K fast

**Part no. 46KV 1A REMOVABLE B/H EXPULSION LINK
46KBR1**

General specifications		
Product name		Eaton Bussmann series medium voltage expulsion fuse
Part no.		46KV 1A REMOVABLE B/H EXPULSION LINK
EAN		5027590481038
Product Length/Depth		787 millimetre
Product height		19.1 millimetre
Product width		19.1 millimetre
Product weight		24.84 gram
Compliances		ANSI C37.42
Certifications		Contact Manufacturer
Product Tradename		None
Product Type		Medium voltage expulsion fuse
Product Sub Type		None
Electrical data		
Amperage Rating		1 A
Voltage rating		46 kV
Current characteristic type		Type K - Complies with ANSI C 37-42 requirements for fast acting K Characteristics
Rated frequency - min		50 Hz
Rated frequency - max		60 Hz
Product specifications		
Application		Primary side transformer protection, feeder protection, capacitor bank protection
Standard		ANSI
Type of termination		Removable buttonhead

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Inserto para fusible de expulsión, media tensión (EC003611)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Expulsion fuse-link, medium voltage (ecl@ss13-27-14-21-28 [AGH830004])		
Corriente nominal	A	1
Tensión nominal	kV	46
Tipo de tensión		CA
Frecuencia nominal (medida)	Hz	50 - 60
Curva de disparo		K
Tipo de terminal		Cabeza de botón extraíble
Estándar		ANSI