

DATASHEET - SL-LED-R



LED, red, BA15d, 24VAC/DC



Part no. SL-LED-R
Catalog No. 215279
Alternate Catalog No. SL-LED-R

Delivery program

Product range			SL signal towers
Single unit/Complete unit			Stand-alone device
			Socket size BA-15d
Lifespan to EN 60064 at $t_a = +25\text{ °C}$	t_{mean} (AC)	h	100000
Rated operational voltage	U_e	V	18 - 30 V AC 50/60 Hz 18 - 30 V DC
Rated operational current	I_e	mA	13 - 50
Colour			
Connection to SmartWire-DT			no

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	55

Technical data ETIM 5.0

Lamps (EG000028) / Indication- and signalling lamp (EC000399)			
Electric engineering, automation, process control engineering / Lighting installation, device / Light medium / Indication- and signal lamp (ec1@ss8-27-11-06-31 [AKE242010])			
Lamp voltage		V	24 - 30
Luminous flux		lm	0
Socket			BA15d
Lamp			LED
Lamp shape			-
Halogen			No
Krypton			No
Xenon			No
Colour			Red
Colour temperature		K	0
Diameter		mm	0
Total length		mm	42
Suitable for torches			No
Suitable for pointer			Yes
Nominal current		mA	50
Lamp power		W	1,5
Average nominal lifespan		h	100000

Approvals

Product Standards			IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			012528

CSA Class No.		3211-03
North America Certification		UL listed, CSA certified