



Фазная шина; 1Ph; 10 кв. мм; вилочный разъём; 6 установочных мест

Тип **EVG-1PHAS/6MODUL**
Каталог № **215638**

Abbildung ähnlich

Программа поставок

Основная функция		Сборная шина
Основная функция дополнительного оснащения		Сборная шина для линейного защитного автомата Сборная шина для дифференциальной защиты Сборная шина для переключателя комбинированной защиты FI/LS
Тип сборной шины		однофазный
Ассортимент		EVG

Технические характеристики согласно ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Электротехника, электроника, системы автоматизации / Низковольтная коммутационная техника / Component for low-voltage switching technology / Phase busbar (ecI@ss10.0.1-27-37-13-06 [ACN992011])			
Number of phases			1
Number of poles			1
Suitable for number of devices			6
Pitch dimensions		mm	0
Cross section		mm ²	10
Length		mm	104
Number of modular spacings			6
Rated permanent current I _u		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I _q		kA	25
Max. rated operation voltage U _e		V	500
Rated short-time withstand current I _{cw}		kA	0
Suitable for devices with N-busbar			No
Suitable for devices with auxiliary switch			No