



**Фазная шина; 3Ph; 10 кв. мм; вилочный разъём; 13,5 установочных мест**

**Тип** EVG-3PHAS/12MODUL/HI  
**Каталог №** 215658

Abbildung ähnlich

## Программа поставок

Основная функция		Сборная шина
Основная функция дополнительного оснащения		Сборная шина для линейного защитного автомата Сборная шина для дифференциальной защиты Сборная шина для переключателя комбинированной защиты FI/LS
Тип сборной шины		трехфазный + HS
Ассортимент		EVG

## Технические характеристики согласно ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)		
Электротехника, электроника, системы автоматизации / Низковольтная коммутационная техника / Component for low-voltage switching technology / Phase busbar (ecl@ss10.0.1-27-37-13-06 [ACN992011])		
Number of phases		3
Number of poles		3
Suitable for number of devices		4
Pitch dimensions	mm	0
Cross section	mm <sup>2</sup>	10
Length	mm	237
Number of modular spacings		12
Rated permanent current I <sub>u</sub>	A	63
Type of electric connection		Fork
Insulated		Yes
Rated surge voltage	kV	4
Conditioned rated short-circuit current I <sub>q</sub>	kA	25
Max. rated operation voltage U <sub>e</sub>	V	500
Rated short-time withstand current I <sub>cw</sub>	kA	0
Suitable for devices with N-busbar		No
Suitable for devices with auxiliary switch		Yes