

# DATOVÝ LIST - NH FUSE 25A 500V GG/GL SIZE 0



Válcová pojistka, Nízkonapětové, 25 A, AC 500 V, 120 kA, NH0, gL/gG, IEC, dvojitý indikátor, neizolované výstupky k uchycení



Powering Business Worldwide™

Typ **NH FUSE 25A 500V GG/GL SIZE 0**  
Catalog No. **25NHG0B**

Abbildung ähnlich

## Dodavatelský program

Produktový sortiment			Pojistka
Základní funkce			Válcová pojistka
Oblast aplikace			Nízkonapětové
Stanovený proud	I	A	25
Jmenovité napětí			AC 500 V
Konstrukční velikost			NH0
Kategorie užití			gL/gG
Stavový indikátor			dvojitý indikátor
Popis			neizolované výstupky k uchycení
Vypínací zatížitelnost		kA	120
použitelné pro velikost / aplikace			průmyslové
Standardní / schválení			IEC
Tvar			čtvercové tělo s nožovými kontakty
Standardní/Regulace			IEC 60269-2 pojistkový systém A DIN 43620 VDE 0636-2

## Technická data podle ETIM 6.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss8.1-27-14-20-05 [AFZ800012])			
Construction size			NH0
Nominal rated current		A	25
Nominal rated voltage		V	500
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator