

DATASHEET - NH FUSE 25A 500V GG/GL SIZE 0



Fuse-link, low voltage, 25 A, AC 500 V, 120 kA, NH0, gL/gG, IEC, dual indicator, live gripping lugs



Referencia **NH FUSE 25A 500V GG/GL SIZE 0**
Catalog No. **25NHG0B**

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	25
Rated voltage			AC 500 V
Construction size			NH0
Utilization category			gL/gG
Status indicator			dual indicator
Description			live gripping lugs
Breaking Capacity		kA	120
usable for size/applications			industrial
Standard/Approval			IEC
Shape			square body with knife blade contacts
Standards/Regulations			IEC 60269-2 fuse system A DIN 43620 VDE 0636-2

Technical data ETIM 5.0

Circuit breakers and fuses (EG000020) / Fusible para baja tensión tipo NH (EC000055)			
Tecnología electrónica, de automatización y de mando de procesos / Instalación eléctricas, equipo / Inserto de fusibles / Inserto de fusibles de baja tensión (ecl@ss8-27-14-20-05 [AFZ800011])			
Tamaño de construcción			NH0
Corriente nominal		A	25
Tensión nominal		V	500
Categoría de uso			gL/gG (protección de cable/equipo)
Tipo de indicador de estado de fusible			Indicador del estado del fusible de combinación