



Cartuccia fusibile, Bassa tensione, 25 A, AC 500 V, 120 kA, NH0, gL/gG, IEC, indicatore doppio, linguette di impugnatura sotto tensione

Tipo NH FUSE 25A 500V GG/GL SIZE 0
Catalog No. 25NHG0B

Abbildung ähnlich

Programma di fornitura

Assortimento			fusibile
Funzione di base			cartuccia fusibile
campo di validità			Bassa tensione
Corrente nominale d'impiego	I	A	25
Tensione nominale d'impiego			AC 500 V
Grandezza			NH0
Classe di funzionamento			gL/gG
Esecuzione indicatore			indicatore doppio
Descrizione			linguette di impugnatura sotto tensione
potere di apertura		kA	120
Utilizzo			industriale
Standard/Approvazione			IEC
Forma			corpo quadrato con contatti a coltello
Standard/Norme			IEC 60269-2 Sistema di fusibili A DIN 43620 VDE 0636-2

Dati tecnici secondo ETIM 6.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss8.1-27-14-20-05 [AFZ800012])			
Construction size			NH0
Nominal rated current		A	25
Nominal rated voltage		V	500
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator