

**Emergency stop/emergency switching off pushbutton, RMQ-Titan,
Mushroom-shaped, 38 mm, Non-illuminated, Turn-to-release function,
Red, yellow, RAL 3000**



Part no. M22-PVT
263467
EL Number 4355405
(Norway)

General specifications		
Product name		Eaton Moeller® series M22 Emergency stop/emergency switching off pushbutton
Part no.		M22-PVT
EAN		4015082634674
Product Length/Depth		38 millimetre
Product height		70 millimetre
Product width		38 millimetre
Product weight		0.045 kilogram
Compliances		CE Marked
Certifications		UL 508 CSA Std. C22.2 No. 94-91 EN 60947-5 CSA Std. C22.2 No. 14-05 IEC 60947-5 VDE CSA Class No.: 3211-03 CSA-C22.2 No. 94-91 CSA File No.: 012528 UL File No.: E29184 CSA CSA-C22.2 No. 14-05 CE UL VDE 0660 IEC/EN 60947 IEC/EN 60947-5 UL Category Control No.: NKCR GL LR DNV
Product Tradename		M22
Product Type		Emergency stop/emergency switching off pushbutton
Product Sub Type		None
Catalog Notes		Max. number of contacts: four M22-(C)K01, ...10 or two M22-(C)K02, ...20, ...11
Features & Functions		
Bezel color		Other
Base color		Yellow
Bezel material		Other
Color		Red
Design		Mushroom-shaped Classical
Features		Tamper-proof (according to ISO 13850, EN 418)
Illumination		Non-illuminated
RAL-number		3000
Unlocking method		Turn-release
General information		
Degree of protection		IP67/IP69K NEMA 4X, 13
Lifespan, mechanical		100,000 Operations
Opening diameter		22.5 mm
Operating frequency		600 Operations/h
Product category		RMQ-Titan
Size		Front dimensions: 35 mm
Suitable for		Emergency stop
Type		Controlled stop pushbutton/emergency-stop button

Ambient conditions, mechanical		
Mounting position		As required
Shock resistance		Mechanical, According to IEC/EN 60068-2-27 50 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		70 °C
Climatic proofing		Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Communication		
Connection to SmartWire-DT		No
Actuator		
Actuating force		50 N
Actuator color		Red
Actuator diameter		38 mm
Actuator function		Turn-to-release Switching function latching
Contacts		
Force for positive opening - min		0 N
Design verification		
Equipment heat dissipation, current-dependent P _{vid}		0 W
Heat dissipation capacity P _{diss}		0 W
Heat dissipation per pole, current-dependent P _{vid}		0 W
Rated operational current for specified heat dissipation (I _n)		0 A
Static heat dissipation, non-current-dependent P _{vs}		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		Not applicable.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Front element for mushroom push-button (EC001038)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Front element for mushroom push-button actuators (ecl@ss10.0.1-27-37-12-12 [AKF030014])		
Colour button		Red
Construction type lens		Round
Diameter cap	mm	38

Hole diameter	mm	22.5
Width opening	mm	0
Height opening	mm	0
Degree of protection (IP)		IP67/IP69K
Degree of protection (NEMA)		4X, 13
Type of button		High
Suitable for illumination		No
With lighting		No
Supply voltage lamp	V	0
Switching function latching		Yes
Spring-return		No
With front ring		No
Material front ring		Other
Colour front ring		Other
Suitable for emergency stop		Yes
Unlocking method		Turn-release