



Trykknapp, 250V, 16A, 1L

Type **Z-PU/S**  
 Catalog No. **276291**

### Tekniske data etter ETIM 7.0

Enheter for skap- / overflatemontering (EG000062) / Trykknapp for DIN-skinne (EC001546)

Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Push button for distribution board (ec1@ss10.0.1-27-14-23-02 [AFZ814014])

Antall NC-kontakter			0
Antall NO-kontakter			1
Antall vekselkontakter			0
Brytestrøm		Amp	16
Vekselspanning		Volt	250
Spenningsstype			AC
Med signallampe			Nei
Hettefarge			Ikke relevant
Lampe			Ikke relevant
Lampesokkel			Ikke relevant
Maks lampeeffekt		Watt	0
Lampespenning		Volt	0 - 0
Farge på knapp			Grønn
Bredde i antall modulmellomrom			1
Innbyggingsdybde		Millimeter	60
Beskyttelsesklasse IP			IP40