



EV busbars 3Ph., 16HP, 63A for PLS. CLS. PKN., PFIM, PFHM, PFNM

Part no. EVG-3PHAS/16MODUL
Catalog No. 285381

EL-Nummer (Norway) 1657145

Similar to illustration

Delivery program

Basic function		Busbar
Basic function accessories		Busbar for miniature circuit-breaker Busbar for residual-current circuit-breakers Busbar for combined residual-current/power circuit-breaker
Busbar type		Three-phase
Product range		EVG

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ecl@ss10.0.1-27-37-13-06 [ACN992011])		
Number of phases		3
Number of poles		3
Suitable for number of devices		5
Pitch dimensions	mm	0
Cross section	mm ²	10
Length	mm	286
Number of modular spacings		16
Rated permanent current I _u	A	63
Type of electric connection		Fork
Insulated		Yes
Rated surge voltage	kV	4
Conditioned rated short-circuit current I _q	kA	25
Max. rated operation voltage U _e	V	415
Rated short-time withstand current I _{cw}	kA	0
Suitable for devices with N-busbar		No
Suitable for devices with auxiliary switch		No